


Pump Your Needs.




**WELCO's easy ordering system
can match the best product to the customer's needs**

WP1000 / WP1100 PERISTALTIC PUMP SELECTION GUIDE


A specification of WELCO Peristaltic pumps can be determined by many combination of parts.

Please select each parts according to your requirement.



2 Pump tube type: Material (Selectable according to fluid type)

WP10 - P 1/8 - - - -

Tube type	Product Description	Regulatory compliance/meets
PHARMED BPT P 	*Great resistant to general chemicals, acid, alkali and oxidizing agents *Compatible with virtually all commercial cleaners and sanitizers *Lasts up to 30 times longer than silicone tubes.	USP Class VI
TYGON A-60-G (Norprene A-60-G) N 	*Lasts and perform better than EPDM and other speciality rubber tubes *Ozone and UV Light resistant *Applicable to soap and disinfectant dispensing, printing ink transfer, and etc...	-
TYGON A-60-F (Norprene A-60-F) NF 	*Food process tube for critical processing applications in the food, dairy and cosmetic industries. *Compatible with virtually all commercial cleaners and sanitizers *Great resistant to general chemicals, acid, alkali and oxidizing agents	FDA 21 CFR Part 177.2600 NSF 51 3-A
TYGON 3355/3350 S 	*High-performance and platinum-cured silicone tube *Ultra-smooth inner bore reduces potential for particle entrapment *Excellent fluid flow characteristics.	FDA 21 CFR Part 177.2600 USP Class VI 3-A (3350 only)
Versilon F-5500-A (Fluran F-5500-A) F 	*A proprietary fluorelastomer tube *Excellent resistance to corrosive chemicals, oils, fuels and solvents *Ozone and UV Light resistant	-
Versilon 2001 (TYGON 2001) U 	*Plasticizer-free chemical resistant tube. *Great resistant to a wide range of fluids that typically destroy PVC products *Applicable to soap and detergent dispensing, ink transfer, water purification lines, food, beverage and chemical transfer	FDA 21 CFR Part 177.2600
TYGONS3 E-LFL (TYGON E-LFL) EL 	*Non-DEGO tube for laboratory, Food & Beverage and Biopharmaceutical Applications *Longest flex life in any clear Tygon tubes *Extremely low particle spallation for sensitive fluid applications	FDA 21 CFR Part 177.2600 USP Class VI NSF-51
TYGOPRENE XL-60 XL 	*Alternative to silicones and PVC when longer pump tube life is required *Excellent resistance to a wide range of fluids, including acids and bases *Greatly reduce the risk of fluid contamination	FDA 21 CFR Part 177.2600 NSF 51
W TUBE W 	*Dual-wall tube which has excellent resistant to chemicals, acid, alkali. *Inner layer: Polyolefin Outer layer: Thermoplastic Elastomers	-

Note: TYGON, Pharmed, Norprene, Fluran and Tygoprene, Versilon are manufactured by Saint-Gobain Group.

Note: When selecting tubes with a 3/16" inner diameter, as long as there are no specification or shape-related issues, use of the WP1100 is recommended.

3 Pump tube type: Tube size (Selectable according to the tube material and number of rollers)

WP1000

Model name (inner diameter)	1/16	3/32	1/8	4
Inner diameter	1.6mm (1/16")	2.4mm (3/32")	3.2mm (1/8")	4mm (-)
Available tube material	P / NF	S / P / NF	All type (of)	P / NF / W
Number of rollers	2 / 4	2 / 4	2 / 4	2 / 4

WP1100

Model name (inner diameter)	3/16	1/4
Inner diameter	4.8mm (3/16")	6.4mm(1/4")
Available tube material	ALL type except for XL	ALL type except for EL,XL
Number of rollers	2 / 4	2

Caution: Tube type F3/16", EL1/8", EL3/16" and U3/16" cannot be used with four rollers due to its characteristic.

Flow amount benchmark (flow amount per rotation)

Inside diameter of tube (inches)	1.6mm (1/16")	2.4mm (3/32")	3.2mm (1/8")	4mm	4.8mm (3/16")	6.4mm(1/4")
Number of rollers	2	4	2	4	2	4
WP1000 Flow amount (mL)	-	0.2	0.5	0.45	0.9	0.8
					1.45	1.2
					1.95	1.6
					3.0	-

Caution: The above table describes the initial benchmark flow amounts during water suction. This may vary considerably depending on the tube type, use period, ambient temperature, and lot tolerances, etc. Measure the specifications with reasonable leeway.




4 Geared motor types





DC Brush Motor & Gear

WP10 - P 1/8 DS - - - -
↑


24VDC Brush Motor & Gear: Three types are selectable (low, medium and high speeds)



12VDC Brush Motor & Gear: Two types are selectable (low and medium speeds)




Motor wiring and terminal dimensions diagrams




1. The consumption current described above is the value during normal operations. An approximately threefold inrush current occurs during rotation start up.
2. The RPM described above is the benchmark value when 100mNm load is applied to each motors. This may vary depending on tube type and operating conditions. Design an application with enough margin upon an evaluation under actual conditions.
3. Short circuit between terminals may occur due to end of motor life or short circuit between commutator slits by specific operating environment and condition. In order to prevent circuit burnout, please take protective measures such as using fuses.

Dimensions (unit: mm)

WP1000




WP1100




WP1000

Cutting hole dimensions



WP1100

Cutting hole dimensions











WP10 - P 1/8 IG - - - -
↑

High Performance DC Brush Motor & Gear

24VDC Brush Motor & Gear: Three types are selectable (low, medium and high speeds)





12VDC Brush Motor & Gear: Three types are selectable (low and medium speeds)



1. The consumption current described above is the value during normal operations. An approximately threefold inrush current occurs during rotation start up.
2. The RPM described above is the benchmark value when 100mNm load is applied to each motors. This may vary depending on tube type and operating conditions. Design an application with enough margin upon an evaluation under actual conditions.
3. Short circuit between terminals may occur due to end of motor life or short circuit between commutator slits by specific operating environment and condition. In order to prevent circuit burnout, please take protective measures such as using fuses.



Dimensions (unit: mm)

WP1000




Weight: ID/IF/JD/JF type 250g
IG/JG type 255g

WP1100



Weight: ID/IF/JD/JF type 265g
IG/JG type 270g


Motor wiring and terminal dimensions diagrams




(unit: mm)

Cutting hole dimensions

WP1000



WP1100





WP10 - P 1/8 PM 2 - - -

DC Brushless Motor & Gear

Three types are selectable (medium and high speeds)

Geared motor Specification


Geared motor model	PM type	PD type	PL type (WP1100 only)
Configuration	Brushless motor & 1:64 Gear head	Brushless motor & 1:42 Gear head	Brushless motor & 1:8 Gear head
Operation Voltage *1	DC16V to DC24V	DC16V to DC24V	DC16V
Current *2	Less than 300mA	Less than 400mA	Less than 700mA
Motor Speed (rpm)	Approx. 50 to 70rpm at DC16 to 24V (100mNm Load)	Approx. 75 to 110rpm at DC16 to 24V (100mNm Load)	Approx. 348rpm at DC16V *3 (100mNm Load)
Direction of Rotation	CW		
Motor Rated Temperature	less than 70°C		
Motor lock protection	IC is integrated into the motor as thermal protection. The motor power shuts down automatically when the IC reaches a predefined temperature. There is no guarantee for recovery once it shuts down.		
	2sec TYP		
Life	If the motor locks up, the motor power will be shut down within 15 seconds		
	5,000hr (Geared motor) *Not a guaranteed value.		

*1.The lowest operation voltage may vary depending on the tube type, tube size, ambient temperature, etc. Please contact your sales representative to get help when you operate by lower voltage.

*2.Caution: The consumption current described above is the value during normal operations. An approximately threefold inrush current occurs during rotation startup.

*3.The flow rate of the PL (6.4mm) type is lower than the value calculated by the flow rate per rotation number of rotations, and is approximately 700mL per minute.

Motor Wiring Information




Circuit protection


There is no circuit protection against overvoltage and wrong connection. Do not apply surge voltages that exceed the rated voltage and not to connect to the incorrect polarity.

Dimensions (unit: mm)

- WP10 - PM
- WP10 - PD



- WP11 - PM
- WP11 - PD






WP10 - P 1/8 **PM** 2 - - -

DC Brushless Motor & Gear

Three types are selectable (medium and high speeds)

Dimensions (unit: mm)


■ WP11 - □ □ PL




Weight: 315g

Cutting hole dimensions

■ WP1000



■ WP1100





WP10 - P 1/8 **FB** - - - -

Stepper Motor & Gear




Four types of stepper motors can be selected according to the application and the product series

Geared motor Specification

Geared motor model	FB type	BA type	GA type	GD type
Configuration	Hybrid stepper motor & 1: 64 Gear ratio	Hybrid stepper motor & 1: 8 Gear ratio	Hybrid stepper motor & 1:8 Gear ratio	Hybrid stepper motor & 1:42 Gear ratio
Number of phases and motor type	2 phase / BI polar system		2 phase / UNI polar system	
Rated Voltage	1.92V	1.76V	3.5V	
Rated Current	0.8A / Phase	1.1A / Phase	1.2A / Phase	
Step Angle	0.0141° (Half step)	0.1125° (Half step)	0.1125° (Half step)	0.0216° (Half step)
Motor Speed (rpm)	0 to 20rpm	20 to 150rpm	20 to 150rpm	0 to 29rpm
Duty Ratio	Max. 50%			
Winding Resistance	2.4Ω±10%	1.6Ω±10%	2.9Ω±10%	
Inductance	2.5mH	2.6mH	4.0mH	
Motor Insulation Class	B			
Motor Rated Temperature	less than 80°C			
Life	5,000hr (Geared motor) *Not a guaranteed value.			




Dimensions (unit: mm)

WP10 - BA






Weight: 322g

WP10 - FB



Weight: 264g

WP10 - GA




Weight: 365g





Four types of stepper motors can be selected according to the application and the product series

■ WP10 - □□ GD



Weight: 380g

■UNI POLAR Winding Diagram



6 Tube fitting type: Varied lineup that is selectable according to requirements

WP10 — P 1/8 DS 2 — **W4** — —



W4

- Connectable hose sizes (OD)
1/4"(6.4mm) or 6mm
- Available pump tube sizes & pump series
WP1000: 1/8"(3.2mm), 4mm,
WP1100: 3/16"(4.8mm), 1/4"(6.4mm)

Fitting consists of compression nut, sleeve and insert. Supports various hose hardnesses.



WM3

- Connectable hose sizes (OD)
3mm
- Available pump tube sizes & pump series
WP1000: 1/16"(1.6mm), 3/32"(2.4mm),
1/8"(3.2mm)
WP1100: N/A

Fitting consists of compression nut and sleeve. Supports various hose hardnesses
Nut and sleeve will vary according to hose size.



WM4

- Connectable hose sizes (OD)
4mm
- Available pump tube sizes & pump series
WP1000: 1/16"(1.6mm), 3/32"(2.4mm),
1/8"(3.2mm)
WP1100: N/A

Fitting consists of compression nut and sleeve. Supports various hose hardnesses
Nut and sleeve will vary according to hose size.



J8

- Connectable hose sizes (OD)
1/8"(3.2mm) (Nylon or Polyethylene)
- Available pump tube sizes & pump series
WP1000: 3/32"(2.4mm), 1/8"(3.2mm)
WP1100: N/A

Nut and sleeve are integrated. Excellent workability.
Suitable for polyethylene, nylon and other plastic hoses.



J4

- Connectable hose sizes (OD)
1/4"(6.4mm) (Nylon or Polyethylene)
- Available pump tube sizes & pump series
WP1000: 1/8"(3.2mm), 4mm,
WP1100: 3/16"(4.8mm), 1/4"(6.4mm)

Nut and sleeve are integrated. Excellent workability.
Suitable for polyethylene, nylon and other plastic hoses.



WI6

- Connectable hose sizes (OD)
6mm (Nylon or Polyethylene)
- Available pump tube sizes & pump series
WP1000: 1/8"(3.2mm), 4mm,
WP1100: 3/16"(4.8mm), 1/4"(6.4mm)

Nut and sleeve are integrated. Excellent workability.
Suitable for polyethylene, nylon and other plastic hoses.



WT6

- Connectable hose sizes
6mm (Note: ID size)
- Available pump tube sizes & pump series
WP1000: 1/8"(3.2mm), 4mm,
WP1100: 3/16"(4.8mm), 1/4"(6.4mm)

Barbed type. Inserted directly into hose and used.



H (No Fitting)

- Connectable hose sizes (OD)
N/A
- Available pump tube sizes & pump series
WP1000: 1/8"(3.2mm), 4mm,
WP1100: 3/16"(4.8mm), 1/4"(6.4mm)

No fitting. For the case in which a customer connects their own original fitting, or when using a special length pump tube.
Note: If the pump tube has a large diameter, the flow rate tolerance should be increased.

7 Color variation

A 5-color lineup that can be classified for use according to the type of liquids used

WP10 - P 1/8 DS 2 - W4 - B



B: Blue



G: Green



C: Clear



R: Red



Y: Yellow



UV: Black
(Special order item
Only for WP1000)

8 Using an optional panel

There is also a lineup of panels to which the pump can be easily mounted


WP1000 - P 1/8 DS 2 - W4 - B P

P = with bracket

N or Blank = without bracket



Option bracket dimensions (unit: mm)



Thickness: 1.2mm
Material properties: SUS304

General specifications

Recommended installation height	2.0m max
Liquid temperature range	5 to 50°C (41°F to 122°F)
Specified environment temperature range	0 to 50°C (32°F to 122°F)
Specified ambient humidity range	20% to 80% (with no condensation)
Certifications&Approvals	    

Precautions

- When selecting a tube, the customer should perform a verification test to verify the chemical suitability according to the usage environment and the intended application.
- Regardless of the pump tube
- This product was not designed for
- This product is not waterproof
- Numerical data listed in this
- There is a tendency for the different lots may have different



WELCO Co.,
3-3-1 Sumiyoshi-cho, Fukuoka
Please see the web site for

PeriPump GmbH | Badenerstrasse 816 | CH-8048 Zürich
Tel: +41 43 811 75 02 | contact@peripump.eu | www.peripump.eu